



Catalog No. CR305K103

Description:

UPC No

Home > Contactors & Starters > NEMA Contactors > 300 Line Full Voltage Magnetic Contactors

NEMA Rated Full Voltage Contactors. Magnetic Contactors. Single-phase, One- and Two-Pole. Nonreversing, Open, NEMA Type 1, 3R, 12, 4/4X. NEMA Sizes 00-9. 600 Volts Maximum 50/60 Hertz. CR305, Single-Phase, 2-Pole Magnetic Contactors NEMA sizes 00-6. Motor full-load current should not exceed continuous ampere rating of contactor.

Descriptors

| | |
|-------------|-------------------------------------------|
| Category | 300 Line Full Voltage Magnetic Contactors |
| GO Schedule | 10G |

Specifications

| | |
|--------------------|-------------|
| Continuous Current | 30 A |
| Enclosure Type | NEMA Type 1 |
| Horsepower | 3 hp |