



**Catalog No. CR305K602**

**Description:**

**UPC No**

**Home > Contactors & Starters > NEMA Contactors > 300 Line Full Voltage Magnetic Contactors**

NEMA Rated Full Voltage Contactors. Magnetic Contactors. Single-phase, One- and Two-Pole. Nonreversing, Open, NEMA Type 1, 3R, 12, 4/4X. NEMA Sizes 00-9. 600 Volts Maximum 50/60 Hertz. CR305, Single-Phase, 2-Pole Magnetic Contactors NEMA sizes 00-6. Motor full-load current should not exceed continuous ampere rating of contactor.

**Descriptors**

Category	300 Line Full Voltage Magnetic Contactors
GO Schedule	10G

**Specifications**

Continuous Current	30 A
Enclosure Type	NEMA Type 3R
Horsepower	2 hp