



Catalog No. CR305S102AEA

Description:

UPC No

Home > Contactors & Starters > NEMA Contactors > 300 Line Full Voltage Magnetic Contactors

Contactors, NEMA, Full Voltage, Non-Reversing, NEMA Size: 1, Maximum Voltage: 600 VAC, Amp Rating: 27 Amp, Horsepower Rating: 7 1/2 @ 230 VAC, Coil Voltage: 115 VAC @ 60 Hz, Enclosure Type: NEMA Type 1, Dimensions: 6 Inch W x 10 Inch H x 4.63 Inch D, Features: Supplied with 1 Normally Open Auxiliary Contact CR305S10

Descriptors

| | |
|-------------|---|
| Category | 300 Line Full Voltage Magnetic Contactors |
| GO Schedule | 10G |

Specifications

| | |
|--------------------|-------------|
| Continuous Current | 30 A |
| Enclosure Type | NEMA Type 1 |