

Catalog No. ELL1/230-G

Description: PVC CTD ELBOW 30D 1/2IN STEEL GRAY

UPC No 704508027506

Home > Cable Protection Systems > Ocal > Electrical conduit elbow

Standard Radius Elbow, 40 Mil PVC Coated, Pipe Size 1/2 Inch/16 Metric, Angle 30 Degrees, Radius 4 Inch/101.60 Millimeters, Offset 6 Inch/152.40 Millimeters, Straight End 2 Inch/50.80 Millimeters, Unbent Length 10.28 Inch/261.19 Millimeters, Hot-Dip Galvanized Rigid Steel, Gray

Representative Image

Descriptors

Category	Electrical conduit elbow
Special Features	Color-Coded Thread Protectors for Easy Identification of Conduit Size
Application	To Change Direction for Threaded, Rigid Conduit or When Terminating at a Box or Fitting

Specifications

Material	Steel
Color	Gray
Finish	Hot-Dipped Galvanized

Classifications

Brand Name	Ocal
------------	------

Dimensions

Length	10.28 in , 261.19 mm
Trade Size	1/2 in , 16 mm

ETIM	EC001493 Bend for cable protection tubes
Material	Metal
Material quality	Steel
Surface protection	Hot dip galvanized
Colour	Other
Model	Rigid
Shape	Outer - and inner side plain
Inner diameter	16 mm
Angle of bow	30 °

by ABB