



Catalog No. ELL11/245SA-G

Description: PVC CTD ELBOW 45D 1-1/2IN ALUM GRY

UPC No 704508369989

Home > Cable Protection Systems > Ocal > Electrical conduit elbow

Standard Radius Elbow, 40 Mil PVC Coated, Pipe Size 1-1/2 Inch/41 Metric, Angle 45 Degrees, Radius 8-1/4 Inch/209.55 Millimeters, Offset 11 Inch/279.40 Millimeters, Straight End 2-3/4 Inch/69.85 Millimeters, Unbent Length 18.46 Inch/468.86 Millimeters, Rigid Aluminum, Gray

Descriptors

Category	Electrical conduit elbow
Special Features	Color-Coded Thread Protectors for Easy Identification of Conduit Size
Application	To Change Direction for Threaded, Rigid Conduit or When Terminating at a Box or Fitting

Specifications

Material	Aluminum
Color	Gray
Finish	PVC Coated

Classifications

Brand Name	Ocal
------------	------

Dimensions

Length	18.46 in , 468.86 mm
Trade Size	1-1/2 in , 41 mm

ETIM	EC001493 Bend for cable protection tubes
Material	Metal
Material quality	Aluminium
Surface protection	Untreated
Colour	Other
Model	Rigid
Shape	Outer - and inner side plain
Inner diameter	41 mm
Angle of bow	45 °

by ABB