



Catalog No. ELL11/260-G

Description: PVC CTD ELBOW 60D 1-1/2IN STEEL GRY

UPC No 704508040741

Home > Cable Protection Systems > Ocal > Electrical conduit elbow

Standard Radius Elbow, 40 Mil PVC Coated, Pipe Size 3-1/2 Inch/91 Metric, Angle 90 Degrees, Radius 15 Inch/381 Millimeters, Offset 20-3/4 Inch/527.05 Millimeters, Straight End 5-3/4 Inch/146.05 Millimeters, Unbent Length 35.06 Inch/890.57 Millimeters, Hot-Dip Galvanized Rigid Steel, Gray

Descriptors

Category	Electrical conduit elbow
Special Features	Color-Coded Thread Protectors for Easy Identification of Conduit Size
Application	To Change Direction for Threaded, Rigid Conduit or When Terminating at a Box or Fitting

Specifications

Material	Steel
Color	Gray
Finish	Hot-Dipped Galvanized

Classifications

Brand Name	Ocal
------------	------

Dimensions

Length	35.06 in , 890.57 mm
Trade Size	3-1/2 in , 91 mm

Compliance and Certifications

RoHS	RoHS3 Compliant
REACH	REACH 253 Compliant
TSCA	TSCA Section 6(h) Compliant