

Catalog No. ELL11/445SA-G

Description: PVC CTD ELBOW 45D 1-1/4IN ALUM GRAY

UPC No 704508029586

Home > Cable Protection Systems > Ocal > Electrical conduit elbow

Standard Radius Elbow, 40 Mil PVC Coated, Pipe Size 1-1/4 Inch/35 Metric, Angle 45 Degrees, Radius 7-1/4 Inch/184.15 Millimeters, Offset 9-1/2 Inch/241.30 Millimeters, Straight End 2-1/4 Inch/57.15 Millimeters, Unbent Length 15.89 Inch/403.56 Millimeters, Rigid Aluminum, Gray

Representative Image

Descriptors

Category	Electrical conduit elbow
Special Features	Color-Coded Thread Protectors for Easy Identification of Conduit Size
Application	To Change Direction for Threaded, Rigid Conduit or When Terminating at a Box or Fitting

Specifications

Material	Aluminum
Color	Gray
Finish	PVC Coated

Classifications

Brand Name	Ocal
------------	------

Dimensions

Length	15.89 in , 403.56 mm
Trade Size	1-1/4 in , 35 mm

ETIM	EC001493 Bend for cable protection tubes
Material	Metal
Material quality	Aluminium
Surface protection	Untreated
Colour	Other
Model	Rigid
Shape	Outer - and inner side plain
Inner diameter	35 mm
Angle of bow	45 °

by ABB