



Representative Image

Catalog No. ELL145SA-G

Description: PVC CTD ELBOW 45D 1IN ALUM GRAY

UPC No 704508426811

Home > Cable Protection Systems > Ocal > Electrical conduit elbow

Standard Radius Elbow, 40 Mil PVC Coated, Pipe Size 1 Inch/27 Metric, Angle 45 Degrees, Radius 5-3/4 Inch/146.05 Millimeters, Offset 8 Inch/203.20 Millimeters, Straight End 2-1/4 Inch/57.15 Millimeters, Unbent Length 13.53 Inch/343.71 Millimeters, Rigid Aluminum, Gray

Descriptors

Category	Electrical conduit elbow
Special Features	Color-Coded Thread Protectors for Easy Identification of Conduit Size
Application	To Change Direction for Threaded, Rigid Conduit or When Terminating at a Box or Fitting

Specifications

Material	Aluminum
Color	Gray
Finish	PVC Coated

Classifications

Brand Name	Ocal
------------	------

Dimensions

Length	13.53 in , 343.71 mm
Trade Size	1 in , 27 mm

Compliance and Certifications

RoHS	RoHS3 Compliant
TSCA	TSCA Section 6(h) Compliant

ETIM	EC001493 Bend for cable protection tubes
Material	Metal
Material quality	Aluminium
Surface protection	Untreated
Colour	Other
Model	Rigid

by ABB

ETIM	EC001493 Bend for cable protection tubes
Shape	Outer - and inner side plain
Inner diameter	27 mm
Angle of bow	45 °