

## Catalog No. ELL21/245-G

**Description:** PVC CTD ELBOW 45D 2-1/2IN STL GRAY

**UPC No** 704508370268

**Home > Cable Protection Systems > Ocal > Electrical conduit elbow**

Standard Radius Elbow, 40 Mil PVC Coated, Pipe Size 2-1/2 Inch/63 Metric, Angle 45 Degrees, Radius 10-1/2 Inch/266.70 Millimeters, Offset 14 Inch/355.60 Millimeters, Straight End 3-1/2 Inch/88.90 Millimeters, Unbent Length 23.49 Inch/596.73 Millimeters, Hot-Dip Galvanized Rigid Steel, Gray

Representative Image

### Descriptors

|                  |                                                                                         |
|------------------|-----------------------------------------------------------------------------------------|
| Category         | Electrical conduit elbow                                                                |
| Special Features | Color-Coded Thread Protectors for Easy Identification of Conduit Size                   |
| Application      | To Change Direction for Threaded, Rigid Conduit or When Terminating at a Box or Fitting |

### Specifications

|          |                       |
|----------|-----------------------|
| Material | Steel                 |
| Color    | Gray                  |
| Finish   | Hot-Dipped Galvanized |

### Classifications

|            |      |
|------------|------|
| Brand Name | Ocal |
|------------|------|

### Dimensions

|            |                      |
|------------|----------------------|
| Length     | 23.49 in , 596.73 mm |
| Trade Size | 2-1/2 in , 63 mm     |

### Compliance and Certifications

|       |                             |
|-------|-----------------------------|
| RoHS  | RoHS3 Compliant             |
| REACH | REACH 247 Compliant         |
| TSCA  | TSCA Section 6(h) Compliant |

|                    |                                          |
|--------------------|------------------------------------------|
| ETIM               | EC001493 Bend for cable protection tubes |
| Material           | Metal                                    |
| Material quality   | Steel                                    |
| Surface protection | Hot dip galvanized                       |
| Colour             | Other                                    |

**by ABB**

|                |                                          |
|----------------|------------------------------------------|
| ETIM           | EC001493 Bend for cable protection tubes |
| Model          | Rigid                                    |
| Shape          | Outer - and inner side plain             |
| Inner diameter | 63 mm                                    |
| Angle of bow   | 45 °                                     |