



Catalog No. ELL21/245SA-G

Description: PVC CTD ELBOW 45D 2-1/2IN ALUM GRAY

UPC No 704508031411

Home > Cable Protection Systems > Ocal > Electrical conduit elbow

Standard Radius Elbow, 40 Mil PVC Coated, Pipe Size 2-1/2 Inch/63 Metric, Angle 45 Degrees, Radius 10-1/2 Inch/266.70 Millimeters, Offset 14 Inch/355.60 Millimeters, Straight End 3-1/2 Inch/88.90 Millimeters, Unbent Length 23.49 Inch/596.73 Millimeters, Rigid Aluminum, Gray

Descriptors

Category	Electrical conduit elbow
Special Features	Color-Coded Thread Protectors for Easy Identification of Conduit Size
Application	To Change Direction for Threaded, Rigid Conduit or When Terminating at a Box or Fitting

Specifications

Material	Aluminum
Color	Gray
Finish	PVC Coated

Classifications

Brand Name	Ocal
------------	------

Dimensions

Length	23.49 in , 596.73 mm
Trade Size	2-1/2 in , 63 mm

ETIM	EC001493 Bend for cable protection tubes
Material	Metal
Material quality	Aluminium
Surface protection	Untreated
Colour	Other
Model	Rigid
Shape	Outer - and inner side plain
Inner diameter	63 mm
Angle of bow	45 °

by ABB