

Catalog No. ELL2111/4-G

Description: PVC CTD ELBOW 11.25D 2IN STEEL GRAY

UPC No 704508033446

Home > Cable Protection Systems > Ocal > Electrical conduit elbow

Standard Radius Elbow, 40 Mil PVC Coated, Pipe Size 2 Inch/53 Metric, Angle 11.25 Degrees, Radius 9-1/2 Inch/241.30 Millimeters, Offset 13 Inch/330.20 Millimeters, Straight End 3-1/2 Inch/88.90 Millimeters, Unbent Length 21.92 Inch/556.83 Millimeters, Hot-Dip Galvanized Rigid Steel, Gray

Descriptors

Category	Electrical conduit elbow
Special Features	Color-Coded Thread Protectors for Easy Identification of Conduit Size
Application	To Change Direction for Threaded, Rigid Conduit or When Terminating at a Box or Fitting

Specifications

Material	Steel
Color	Gray
Finish	Hot-Dipped Galvanized

Classifications

Brand Name	Ocal

Dimensions

Length	21.92 in , 556.83 mm
Trade Size	2 in , 53 mm

Compliance and Certifications

RoHS	RoHS3 Compliant
REACH	REACH 240 Compliant
TSCA	TSCA Section 6(h) Compliant

ETIM	EC001493 Bend for cable protection tubes
Material	Metal
Material quality	Steel
Surface protection	Hot dip galvanized
Colour	Other

by ABB

ETIM	EC001493 Bend for cable protection tubes
Model	Rigid
Shape	Outer - and inner side plain
Inner diameter	53 mm
Angle of bow	11.25 °