

Catalog No. ELL3/445SA-G

Description: PVC CTD ELBOW 45D 3/4IN ALUM GRAY

UPC No 704508024314

Home > Cable Protection Systems > Ocal > Electrical conduit elbow

Standard Radius Elbow, 40 Mil PVC Coated, Pipe Size 3/4 Inch/21 Metric, Angle 45 Degrees, Radius 4-1/2 Inch/114.30 Millimeters, Offset 6-1/2 Inch/165.10 Millimeters, Straight End 2 Inch/50.80 Millimeters, Unbent Length 11.07 Inch/281.14 Millimeters, Rigid Aluminum, Gray

Representative Image

Descriptors

Category	Electrical conduit elbow
Special Features	Color-Coded Thread Protectors for Easy Identification of Conduit Size
Application	To Change Direction for Threaded, Rigid Conduit or When Terminating at a Box or Fitting

Specifications

Material	Aluminum
Color	Gray
Finish	PVC Coated

Classifications

Brand Name	Ocal
------------	------

Dimensions

Length	11.07 in , 281.14 mm
Trade Size	3/4 in , 21 mm

Compliance and Certifications

RoHS	RoHS3 Compliant
REACH	REACH 253 Compliant
TSCA	TSCA Section 6(h) Compliant

ETIM	EC001493 Bend for cable protection tubes
Material	Metal
Material quality	Aluminium
Surface protection	Untreated
Colour	Other

by ABB

ETIM	EC001493 Bend for cable protection tubes
Model	Rigid
Shape	Outer - and inner side plain
Inner diameter	21 mm
Angle of bow	45 °