



Catalog No. ELL415-G

Description: PVC CTD ELBOW 15D 4IN STEEL GRAY

UPC No 704508033606

Home > Cable Protection Systems > Ocal > Electrical conduit elbow

Standard Radius Elbow, 40 Mil PVC Coated, Pipe Size 4 Inch/103 Metric, Angle 15 Degrees, Radius 16 Inch/406.40 Millimeters, Offset 21-3/4 Inch/552.45 Millimeters, Straight End 5-3/4 Inch/146.05 Millimeters, Unbent Length 36.63 Inch/930.47 Millimeters, Hot-Dip Galvanized Rigid Steel, Gray

Descriptors

Category	Electrical conduit elbow
Special Features	Color-Coded Thread Protectors for Easy Identification of Conduit Size
Application	To Change Direction for Threaded, Rigid Conduit or When Terminating at a Box or Fitting

Specifications

Material	Steel
Color	Gray
Finish	Hot-Dipped Galvanized

Classifications

Brand Name	Ocal
------------	------

Dimensions

Length	36.63 in , 930.47 mm
Trade Size	4 in , 103 mm

Compliance and Certifications

RoHS	RoHS3 Compliant
REACH	REACH 253 Compliant
TSCA	TSCA Section 6(h) Compliant

ETIM	EC001493 Bend for cable protection tubes
Material	Metal
Material quality	Steel
Surface protection	Hot dip galvanized
Colour	Other

by ABB

ETIM	EC001493 Bend for cable protection tubes
Model	Rigid
Shape	Outer - and inner side plain
Inner diameter	103 mm
Angle of bow	15 °