



Representative Image

Alternate Catalog No. CA6-11K-F Catalog No. GJL1201318R0001

Description: CA6-11K-F Auxiliary Contact

UPC No 4013614050985

Home > Contactors & Starters > UL Listed IEC Contactors > AF Contactors

CA6-11K-F is an auxiliary contact for side with 2 auxiliary contact and flat pin connection.

Descriptors

Category	AF Contactors
Block Contactor Type	Aux Contact

Specifications

Product Type	Mini Contactors (B6, B7)
Object Classification Code	K
Terminal Type	Flat-Pin Connections
Number of Main Contacts NO	0
Number of Main Contacts NC	0
Maximum Operating Voltage UL/CSA	Auxiliary Circuit 600 V AC / DC
Resistance to Vibrations acc. to IEC 60068-2-6	5g / 5 ... 150 Hz
Number of Auxiliary Contacts NO	1
RoHS Status	Following EU Directive 2011/65/EU
Reference Ambient Air Temperature	Operation -25 ... +55 °C
Rated Operational Voltage	Auxiliary Circuit 12 ... 240 V DC Auxiliary Circuit 12 ... 500 V AC / DC
Number of Auxiliary Contacts NC	1
Maximum Operating Altitude Permissible	2000 m
Standards	IEC/EN 60947-1 IEC/EN 60947-4-1 IEC/EN 60947-5-1 UL 60947-1 UL 60947-4-1
Conventional Free-air Thermal Current	Auxiliary Circuit 6 A
Rated Operational Current AC-15	(240 V) 4 A (24 V) 4 A (380 / 400 V) 3 A (500 V) 2 A
Rated Frequency	Auxiliary Circuit 50 Hz Auxiliary Circuit 60 Hz Auxiliary Circuit DC
Maximum Electrical Switching Frequency	AC-15 600 cycles per hour DC-13 600 cycles per hour
Short-Circuit Protective Devices	gG Type Fuses 10 A
Rated Insulation Voltage	690 V
Secondary Rated Impulse Withstand Voltage	Auxiliary Circuit 6 kV

Specifications

Rated Operational Current DC-13	(110 V) 0.4 A (220 / 240 V) 0.04 A (24 V) 1.5 A
Degree of Protection	IP20

Classifications

ETIM 4	EC000041 - Auxiliary contact block
ETIM 6.0	EC000041 - Auxiliary contact block
ETIM 7	EC000041 - Auxiliary contact block
ETIM 5.0	EC000041 - Auxiliary contact block
eClass	7.0 27371302

Dimensions

Product Net Weight	0.025 kg
Product Net Depth / Length	46.5 mm
Product Net Width	20.3 mm
Product Net Height	48.5 mm

Package Information

Package Level 1 Width	112 mm
Package Level 1 Height	62 mm
Package Level 1 Depth / Length	142 mm
Package Level 1 EAN	4013614412134
Package Level 1 Units	10 piece
Package Level 1 Gross Weight	0.315 kg

Ordering

Minimum Order Quantity	1
Customs Tariff Number	85365080