



Representative Image

## Alternate Catalog No. LB6 Catalog No. GJL1201902R0001

**Description:** LB6 Soldering Socket

**UPC No** 4013614051074

**Home > Contactors & Starters > UL Listed IEC Contactors > AF Contactors**

LB6 Soldering Receptacle 5-pole

### Descriptors

Category	AF Contactors
Block Contactor Type	Accessory

### Specifications

Product Type	Mini Contactors (B6, B7)
Object Classification Code	X
Maximum Operating Voltage UL/CSA	Main Circuit 300 V AC Auxiliary Circuit 300 V AC
Reference Ambient Air Temperature	Operation-25 ... +50 °C Storage-25 ... +55 °C Storage-40 ... +80°C
Standards	UL 60947-1 UL 60947-4-1
Conventional Free-air Thermal Current	Auxiliary Circuit 10 A Main Circuit 10 A
Rated Operational Current AC-3	(500 V) 55 °C 8 A (690 V) 55 °C 3.5 A
Rated Insulation Voltage	690 V

### Classifications

ETIM 4	EC002498 - Accessories for low-voltage switch technology
ETIM 6.0	EC002498 - Accessories for low-voltage switch technology
ETIM 7	EC002498 - Accessories for low-voltage switch technology
ETIM 5.0	EC002498 - Accessories for low-voltage switch technology
eClass	7.0 27379201

### Dimensions

Product Net Weight	0.02kg
Product Net Depth / Length	40 mm
Product Net Width	47.5 mm
Product Net Height	44 mm

**Package Information**

Package Level 1 Width	115 mm
Package Level 1 Depth / Length	280 mm
Package Level 1 Units	10 piece

**Ordering**

Minimum Order Quantity	1
------------------------	---