



Representative Image

Catalog No. GUAN47-G

Description: CONDBOX NTYPE 1-1/4IN OPNG 3.63IN G

UPC No 704508385712

Home > Cable Protection Systems > Ocal > Hazardous location box

PVC Double-Coated Conduit Outlet Box for Hazardous Locations, GUAN Type - L Shape, Pipe Size 1-1/4 Inch/35 Metric, Box is Ductile Iron with Zinc Plating, Cover is Die Cast Aluminum, Cover Opening 3.63 Inch/92.20 Millimeters, Gray

Descriptors

Category	Hazardous location box
Special Features	O-Ring Gasket Provided to Assure NEMA 4 Rating
Application	For Use in Hazardous Locations to Provide Access to Conductors for Pulling, Splicing, Maintenance and Future Changes/upgrades

Specifications

Material	Zinc Plated Iron Body with Aluminum Cover
Color	Gray
Cubic Capacity	31.5 cu in
Knockouts	Yes

Classifications

Brand Name	Ocal
------------	------

Dimensions

Size	1-1/4 Inch/35mm
------	-----------------

Compliance and Certifications

RoHS	RoHS3 Compliant
TSCA	TSCA Section 6(h) Compliant

ETIM	EC002600 Box/housing for surface mounting on the wall/ceiling
Shape	Rectangular
Number of inlets	2
Type of housing feed-through	Thread
Material	Other
Surface protection	Other
Colour	Grey

by ABB

Certification/Standard

CLASS	File Number	Class	CCN	Certificate Number	Library Number
UL	E211925	N/A	QBCR	N/A	N/A