



Representative Image

Catalog No. GUAW14-G

Description: CONDBOX W TYPE 1/2IN OPNG 2IN GRY

UPC No 704508386207

Home > Cable Protection Systems > Ocal > Hazardous location box

PVC Double-Coated Conduit Outlet Box for Hazardous Locations, GUAW Type, Pipe Size 1/2 Inch/16 Metric, Box is Ductile Iron with Zinc Plating, Cover is Die Cast Aluminum, Cover Opening 2.00 Inch/50.80 Millimeters, Gray

Descriptors

Category	Hazardous location box
Special Features	O-Ring Gasket Provided to Assure NEMA 4 Rating
Application	For Use in Hazardous Locations to Provide Access to Conductors for Pulling, Splicing, Maintenance and Future Changes/upgrades

Specifications

Material	Zinc Plated Iron Body with Aluminum Cover
Color	Gray
Cubic Capacity	5.2 cu in
Knockouts	Yes

Classifications

Brand Name	Ocal
------------	------

Dimensions

Size	1/2 Inch/16mm
------	---------------

ETIM	EC002600 Box/housing for surface mounting on the wall/ceiling
Shape	Rectangular
Number of inlets	4
Type of housing feed-through	Thread
Material	Other
Surface protection	Other
Colour	Grey

Certification/Standard

CLASS	File Number	Class	CCN	Certificate Number	Library Number
UL	E211925	N/A	QBCR	N/A	N/A