

Representative Image

## Catalog No. HUB11/2-G

**Description: PVC CTD ZINC HUB CONN 1-1/2IN DGRAY**

**UPC No 704508388249**

**Home > Cable Protection Systems > Ocal > Electrical fittings**

PVC Coated Zinc Hub Connector with Thermoplastic Insulated Throat, Pipe Size 1-1/2 Inch/41 Metric, Overall Diameter 2.75 Inch/69.85 Millimeters, Maximum Panel Thickness 0.25 Inch/6.35 Millimeters, Throat Diameter 1.53 Inch/38.86 Millimeters, Nitrile Rubber (Buna-N) Sealing Ring, Dark Gray

### Descriptors

| | |
|---|---|
| Category | Electrical fittings |
| Special Features | Hexagonal/Splined Body and Locknut Enables Fast and Easy Installation |
| Application | To Positively Bond Conduit to Box or Enclosure |

### Specifications

| | |
|---|---|
| Material | PVC Coated Zinc |
| Color | Dark Gray |
| Temperature Rating | 105 C |

### Classifications

| | |
|---|---|
| Brand Name | Ocal |
| Standard | CSA |

### Dimensions

| | |
|---|---|
| Size | 1-1/2 Inch/41mm |

### Compliance and Certifications

| | |
|---|---|
| RoHS | RoHS3 Compliant |
| TSCA | TSCA Section 6(h) Compliant |

| | |
|---|---|
| ETIM | EC001180 Screw connection for protective metallic hose |
| Nominal diameter | 41 mm |
| Nominal size in inch | 1 1/2 inch |
| Model | Straight |
| Revolving thread | N |
| Construction type | External thread |
| Material housing | Other |

| | |
|---|---|
| ETIM | EC001180 Screw connection for protective metallic hose |
| Surface protection | Other |

**Certification/Standard**

| CLASS | File Number | Class | CCN | Certificate Number | Library Number |
|---|---|---|---|---|---|
| CSA | 4484 | 441202 | N/A | 2163217_2015-01-22 | N/A |