

Representative Image

Catalog No. HUB11/2-G

Description: PVC CTD ZINC HUB CONN 1-1/2IN DGRAY

UPC No 704508388249

Home > Cable Protection Systems > Ocal > Electrical fittings

PVC Coated Zinc Hub Connector with Thermoplastic Insulated Throat, Pipe Size 1-1/2 Inch/41 Metric, Overall Diameter 2.75 Inch/69.85 Millimeters, Maximum Panel Thickness 0.25 Inch/6.35 Millimeters, Throat Diameter 1.53 Inch/38.86 Millimeters, Nitrile Rubber (Buna-N) Sealing Ring, Dark Gray

Descriptors

Category	Electrical fittings
Special Features	Hexagonal/Splined Body and Locknut Enables Fast and Easy Installation
Application	To Positively Bond Conduit to Box or Enclosure

Specifications

Material	PVC Coated Zinc
Color	Dark Gray
Temperature Rating	105 C

Classifications

Brand Name	Ocal
Standard	CSA

Dimensions

Size	1-1/2 Inch/41mm

Compliance and Certifications

RoHS	RoHS3 Compliant
TSCA	TSCA Section 6(h) Compliant

ETIM	EC001180 Screw connection for protective metallic hose
Nominal diameter	41 mm
Nominal size in inch	1 1/2 inch
Model	Straight
Revolving thread	N
Construction type	External thread
Material housing	Other

ETIM	EC001180 Screw connection for protective metallic hose
Surface protection	Other

Certification/Standard

CLASS	File Number	Class	CCN	Certificate Number	Library Number
CSA	4484	441202	N/A	2163217_2015-01-22	N/A