

Representative Image

Catalog No. HUB11/2SA-G

Description: PVC CTD AL HUB CONN 1-1/2IN DGRAY

UPC No 704508388287

Home > Cable Protection Systems > Ocal > Electrical fittings

PVC Coated Aluminum Hub Connector with Thermoplastic Insulated Throat, Pipe Size 1-1/2 Inch/41 Metric, Overall Diameter 2.75 Inch/69.85 Millimeters, Maximum Panel Thickness 0.25 Inch/6.35 Millimeters, Throat Diameter 1.53 Inch/38.86 Millimeters, Nitrile Rubber (Buna-N) Sealing Ring, Dark Gray

Descriptors

Category	Electrical fittings
Special Features	Hexagonal/Splined Body and Locknut Enables Fast and Easy Installation
Application	To Positively Bond Conduit to Box or Enclosure

Specifications

Material	PVC Coated Aluminum
Color	Dark Gray
Temperature Rating	105 C

Classifications

Brand Name	Ocal

Dimensions

Size	1-1/2 Inch/41mm

Compliance and Certifications

RoHS	RoHS3 Compliant
REACH	REACH 253 Compliant
TSCA	TSCA Section 6(h) Compliant

ETIM	EC001180 Screw connection for protective metallic hose
Nominal diameter	41 mm
Nominal size in inch	1 1/2 inch
Model	Straight
Revolving thread	N
Construction type	External thread
Material housing	Other

ETIM	EC001180 Screw connection for protective metallic hose
Surface protection	Other