

Catalog No. JPH1212

Description: HIGH TEMP JOINER NC12 - NC12

UPC No 5020963805462

Home > Cable Protection Systems > Harnessflex > Electrical conduit coupling

Hinged Conduit Joiner for High Temperatures, Straight, Conduit Size A: NC12/NW10, Size B: NC12/NW10, Operating Temperature -40 to 185 Degrees Celsius, RoHS Compliant, IP40 Rating, Medium UV Protection, High Temperature Polyamide (Nylon) with Dark Orange Finish

Representative Image

Descriptors

Category	Electrical conduit coupling
Application	One-Piece Joiner Hinged Fitting. Can Be Used as an In-Line Reducer and Enlarger

Specifications

Material	Polyamide/Nylon
Color	Dark Orange

Classifications

Brand Name	Harnessflex
Standard	RoHS, UL94 V2, ELV EU200/53/EC

Dimensions

Trade Size	NC12 to NC12 , NW10 to NW10
Outside Diameter	16 mm

Compliance and Certifications

RoHS	RoHS3 Compliant
------	-----------------

ETIM	EC001172 Coupler for corrugated plastic hoses
Material	Plastic
Material quality	Polyamide (PA)
Degree of protection (IP)	IP40
Model	Straight
Nominal size	12-12 mm
Colour	Other