

Representative Image

Catalog No. LRELL11/2X1545-G

Description: PVC CTD ELB 45D 1-1/2IN R15IN STL G

UPC No 704508018429

Home > Cable Protection Systems > Ocal > Electrical conduit elbow

Large Radius Elbow, 40 Mil PVC Coated, Pipe Size 1-1/2 Inch/41 Metric, Angle 45 Degrees, Radius 15 Inch/381.00 Millimeters, Offset 2 Feet/609.60 Millimeters, Straight End 9 Inch/228.60 Millimeters, Unbent Length 42 Inch/1,066.80 Millimeters, Hot-Dip Galvanized Rigid Steel, Gray

Descriptors

Category	Electrical conduit elbow
Special Features	Color-Coded Thread Protectors for Easy Identification of Conduit Size
Application	To Change Direction for Threaded, Rigid Conduit or When Terminating at a Box or Fitting

Specifications

Material	Steel
Color	Gray
Finish	Hot-Dipped Galvanized

Classifications

Brand Name	Ocal

Dimensions

Length	42 in , 1,066.8 mm
Trade Size	1-1/2 in , 41 mm

ETIM	EC001493 Bend for cable protection tubes
Material	Metal
Material quality	Steel
Surface protection	Hot dip galvanized
Colour	Other
Model	Rigid
Shape	Outer - and inner side plain
Inner diameter	41 mm
Angle of bow	45 °