

Representative Image

## Catalog No. LRELL11/2X18-G

**Description: PVC CTD ELB 90D 1-1/2IN R18IN STL G**

**UPC No 704508394622**

**Home > Cable Protection Systems > Ocal > Electrical conduit elbow**

Large Radius Elbow, 40 Mil PVC Coated, Pipe Size 1-1/2 Inch/41 Metric, Angle 90 Degrees, Radius 18 Inch/457.20 Millimeters, Offset 2 Feet 4 Inch/711.20 Millimeters, Straight End 10 Inch/254.00 Millimeters, Unbent Length 48 Inch/1,219.20 Millimeters, Hot-Dip Galvanized Rigid Steel, Gray

### Descriptors

| | |
|---|---|
| Category | Electrical conduit elbow |
| Special Features | Color-Coded Thread Protectors for Easy Identification of Conduit Size |
| Application | To Change Direction for Threaded, Rigid Conduit or When Terminating at a Box or Fitting |

### Specifications

| | |
|---|---|
| Material | Steel |
| Color | Gray |
| Finish | Hot-Dipped Galvanized |

### Classifications

| | |
|---|---|
| Brand Name | Ocal |
| Standard | cULus E46453, CSA |

### Dimensions

| | |
|---|---|
| Length | 48 in , 1,219.2 mm |
| Trade Size | 1-1/2 in , 41 mm |

### Compliance and Certifications

| | |
|---|---|
| RoHS | RoHS3 Compliant |
| REACH | REACH 253 Compliant |
| TSCA | TSCA Section 6(h) Compliant |

| | |
|---|---|
| ETIM | EC001493 Bend for cable protection tubes |
| Material | Metal |
| Material quality | Steel |
| Surface protection | Hot dip galvanized |

by ABB

| | |
|---|---|
| ETIM | EC001493 Bend for cable protection tubes |
| Colour | Other |
| Model | Rigid |
| Shape | Outer - and inner side plain |
| Inner diameter | 41 mm |
| Angle of bow | 90 ° |

**Certification/Standard**

| CLASS | File Number | Class | CCN | Certificate Number | Library Number |
|---|---|---|---|---|---|
| CSA | 110787 | 184105 | N/A | 2177301 | N/A |