

Representative Image

Catalog No. LRELL11/2X1845-G

Description: PVC CTD ELB 45D 1-1/2IN R18IN STL G

UPC No 704508017224

Home > Cable Protection Systems > Ocal > Electrical conduit elbow

Large Radius Elbow, 40 Mil PVC Coated, Pipe Size 1-1/2 Inch/41 Metric, Angle 45 Degrees, Radius 18 Inch/457.20 Millimeters, Offset 2 Feet 4 Inch/711.20 Millimeters, Straight End 10 Inch/254.00 Millimeters, Unbent Length 48 Inch/1,219.20 Millimeters, Hot-Dip Galvanized Rigid Steel, Gray

Descriptors

Category	Electrical conduit elbow
Special Features	Color-Coded Thread Protectors for Easy Identification of Conduit Size
Application	To Change Direction for Threaded, Rigid Conduit or When Terminating at a Box or Fitting

Specifications

Material	Steel
Color	Gray
Finish	Hot-Dipped Galvanized

Classifications

Brand Name	Ocal

Dimensions

Length	48 in , 1,219.2 mm
Trade Size	1-1/2 in , 41 mm

ETIM	EC001493 Bend for cable protection tubes
Material	Metal
Material quality	Steel
Surface protection	Hot dip galvanized
Colour	Other
Model	Rigid
Shape	Outer - and inner side plain
Inner diameter	41 mm
Angle of bow	45 °