

Representative Image

Catalog No. LRELL11/4X30-G

Description: PVC CTD ELB 90D 1-1/4IN R30IN STL G

UPC No 704508394929

Home > Cable Protection Systems > Ocal > Electrical conduit elbow

Large Radius Elbow, 40 Mil PVC Coated, Pipe Size 1-1/4 Inch/35 Metric, Angle 90 Degrees, Radius 30 Inch/762 Millimeters, Offset 3 Feet 5 Inch/1,041.40 Millimeters, Straight End 11 Inch/279.40 Millimeters, Unbent Length 69 Inch/1,752.60 Millimeters, Hot-Dip Galvanized Rigid Steel, Gray

Descriptors

Category	Electrical conduit elbow
Special Features	Color-Coded Thread Protectors for Easy Identification of Conduit Size
Application	To Change Direction for Threaded, Rigid Conduit or When Terminating at a Box or Fitting

Specifications

Material	Steel
Color	Gray
Finish	Hot-Dipped Galvanized

Classifications

Brand Name	Ocal
Standard	cULus E46453, CSA

Dimensions

Length	69 in , 1,752.6 mm
Trade Size	1-1/4 in , 35 mm

ETIM	EC001493 Bend for cable protection tubes
Material	Metal
Material quality	Steel
Surface protection	Hot dip galvanized
Colour	Other
Model	Rigid
Shape	Outer - and inner side plain
Inner diameter	35 mm
Angle of bow	90 °

Certification/Standard

CLASS	File Number	Class	CCN	Certificate Number	Library Number
CSA	110787	184105	N/A	2177301	N/A