



Representative Image

Catalog No. LRELL1X18SA-G

Description: PVC CTD ELB 90D 1IN R18IN AL GRY

UPC No 704508014032

Home > Cable Protection Systems > Ocal > Electrical conduit elbow

Large Radius Elbow, 40 Mil PVC Coated, Pipe Size 1 Inch/27 Metric, Angle 90 Degrees, Radius 18 Inch/457.20 Millimeters, Offset 2 Feet 4 Inch/711.20 Millimeters, Straight End 10 Inch/254.00 Millimeters, Unbent Length 48 Inch/1,219.20 Millimeters, Rigid Aluminum, Gray

Descriptors	
Category	Electrical conduit elbow
Special Features	Color-Coded Thread Protectors for Easy Identification of Conduit Size
Application	To Change Direction for Threaded, Rigid Conduit or When Terminating at a Box or Fitting
Specifications	
Material	Aluminum
Color	Gray
Finish	PVC Coated
Classifications	
Brand Name	Ocal
Dimensions	
Length	48 in , 1,219.2 mm
Trade Size	1 in , 27 mm
Compliance and Certifications	
RoHS	RoHS3 Compliant
TSCA	TSCA Section 6(h) Compliant
ETIM	
ETIM	EC001493 Bend for cable protection tubes
Material	Metal
Material quality	Aluminium
Surface protection	Untreated
Colour	Other
Model	Rigid

ETIM	EC001493 Bend for cable protection tubes
Shape	Outer - and inner side plain
Inner diameter	27 mm
Angle of bow	90 °