



Catalog No. LRELL1X3045-G

Description: PVC CTD ELB 45D 1IN R30IN STL GRY

UPC No 704508031169

Home > Cable Protection Systems > Ocal > Electrical conduit elbow

Large Radius Elbow, 40 Mil PVC Coated, Pipe Size 1 Inch/27 Metric, Angle 45 Degrees, Radius 30 Inch/762 Millimeters, Offset 3 Feet 5 Inch/1,041.40 Millimeters, Straight End 11 Inch/279.40 Millimeters, Unbent Length 69 Inch/1,752.60 Millimeters, Hot-Dip Galvanized Rigid Steel, Gray

Descriptors

Category	Electrical conduit elbow
Special Features	Color-Coded Thread Protectors for Easy Identification of Conduit Size
Application	To Change Direction for Threaded, Rigid Conduit or When Terminating at a Box or Fitting

Specifications

Material	Steel
Color	Gray
Finish	Hot-Dipped Galvanized

Classifications

Brand Name	Ocal
------------	------

Dimensions

Length	69 in , 1,752.6 mm
Trade Size	1 in , 27 mm

ETIM	EC001493 Bend for cable protection tubes
Material	Metal
Material quality	Steel
Surface protection	Hot dip galvanized
Colour	Other
Model	Rigid
Shape	Outer - and inner side plain
Inner diameter	27 mm
Angle of bow	45 °