



Catalog No. LRELL2X1260-G

Description: PVC CTD ELB 60D 2IN R12IN STL GRY

UPC No 704508034443

Home > Cable Protection Systems > Ocal > Electrical conduit elbow

Large Radius Elbow, 40 Mil PVC Coated, Pipe Size 2 Inch/53 Metric, Angle 60 Degrees, Radius 12 Inch/304.80 Millimeters, Offset 1 Foot 9 Inch/533.40 Millimeters, Straight End 9 Inch/228.60 Millimeters, Unbent Length 36 Inch/914.40 Millimeters, Hot-Dip Galvanized Rigid Steel, Gray

Descriptors

Category	Electrical conduit elbow
Special Features	Color-Coded Thread Protectors for Easy Identification of Conduit Size
Application	To Change Direction for Threaded, Rigid Conduit or When Terminating at a Box or Fitting

Specifications

Material	Steel
Color	Gray
Finish	Hot-Dipped Galvanized

Classifications

Brand Name	Ocal
------------	------

Dimensions

Length	36 in , 914.4 mm
Trade Size	2 in , 53 mm

ETIM	EC001493 Bend for cable protection tubes
Material	Metal
Material quality	Steel
Surface protection	Hot dip galvanized
Colour	Other
Model	Rigid
Shape	Outer - and inner side plain
Inner diameter	53 mm
Angle of bow	60 °