

Representative Image

## Catalog No. LRELL3/4X18-G

**Description: PVC CTD ELB 90D 3/4IN R18IN STL GRY**

**UPC No 704508013851**

**Home > Cable Protection Systems > Ocal > Electrical conduit elbow**

Large Radius Elbow, 40 Mil PVC Coated, Pipe Size 3/4 Inch/21 Metric, Angle 90 Degrees, Radius 18 Inch/457.20 Millimeters, Offset 2 Feet 4 Inch/711.20 Millimeters, Straight End 10 Inch/254.00 Millimeters, Unbent Length 48 Inch/1,219.20 Millimeters, Hot-Dip Galvanized Rigid Steel, Gray

### Descriptors

| | |
|---|---|
| Category | Electrical conduit elbow |
| Special Features | Color-Coded Thread Protectors for Easy Identification of Conduit Size |
| Application | To Change Direction for Threaded, Rigid Conduit or When Terminating at a Box or Fitting |

### Specifications

| | |
|---|---|
| Material | Steel |
| Color | Gray |
| Finish | Hot-Dipped Galvanized |

### Classifications

| | |
|---|---|
| Brand Name | Ocal |

### Dimensions

| | |
|---|---|
| Length | 48 in , 1,219.2 mm |
| Trade Size | 3/4 in , 21 mm |

### Compliance and Certifications

| | |
|---|---|
| RoHS | RoHS3 Compliant |
| REACH | REACH 253 Compliant |
| TSCA | TSCA Section 6(h) Compliant |

| | |
|---|---|
| ETIM | EC001493 Bend for cable protection tubes |
| Material | Metal |
| Material quality | Steel |
| Surface protection | Hot dip galvanized |
| Colour | Other |

| | |
|---|---|
| ETIM | EC001493 Bend for cable protection tubes |
| Model | Rigid |
| Shape | Outer - and inner side plain |
| Inner diameter | 21 mm |
| Angle of bow | 90 ° |