

Representative Image

# Catalog No. LRELL3/4X24SA-G

**Description: PVC CTD ELB 90D 3/4IN R24IN AL GRY**

**UPC No 704508012588**

**Home > Cable Protection Systems > Ocal > Electrical conduit elbow**

Large Radius Elbow, 40 Mil PVC Coated, Pipe Size 3/4 Inch/21 Metric, Angle 90 Degrees, Radius 24 Inch/609.60 Millimeters, Offset 2 Feet 11 Inch/889.00 Millimeters, Straight End 11 Inch/279.40 Millimeters, Unbent Length 59 Inch/1,498.60 Millimeters, Rigid Aluminum, Gray

## Descriptors

| | |
|---|---|
| Category | Electrical conduit elbow |
| Special Features | Color-Coded Thread Protectors for Easy Identification of Conduit Size |
| Application | To Change Direction for Threaded, Rigid Conduit or When Terminating at a Box or Fitting |

## Specifications

| | |
|---|---|
| Material | Aluminum |
| Color | Gray |
| Finish | PVC Coated |

## Classifications

| | |
|---|---|
| Brand Name | Ocal |

## Dimensions

| | |
|---|---|
| Length | 59 in , 1,498.6 mm |
| Trade Size | 3/4 in , 21 mm |

## Compliance and Certifications

| | |
|---|---|
| RoHS | RoHS3 Compliant |
| REACH | REACH 253 Compliant |
| TSCA | TSCA Section 6(h) Compliant |

| | |
|---|---|
| ETIM | EC001493 Bend for cable protection tubes |
| Material | Metal |
| Material quality | Aluminium |
| Surface protection | Untreated |
| Colour | Other |

| | |
|---|---|
| ETIM | EC001493 Bend for cable protection tubes |
| Model | Rigid |
| Shape | Outer - and inner side plain |
| Inner diameter | 21 mm |
| Angle of bow | 90 ° |