



Representative Image

Catalog No. MINE21/2-G

Description: MINI COND HGR W/SS BOLT 2-1/2IN GRY

UPC No 704508396923

Home > Cable Protection Systems > Ocal > Electrical hangers

PVC Coated Mini Conduit Hanger, Pipe Size 2-1/2 Inch/63 Metric, Rated for Loads up to 500 Pounds (226.80 Kilograms) with a Safety Factor of Three, Includes Stainless Steel Bolt and Nut, Dark Gray

Descriptors

Category	Electrical hangers
Special Features	Includes Stainless Steel Bolt and Nut for Fast, Easy Installation
Application	Rated for Loads of Up to 500 Pounds/226.80kg with a Safety Factor of Three

Specifications

Material	Steel
Color	Dark Gray
Load	Up to 500 pounds , Up to 226.80 kg

Classifications

Brand Name	Ocal
------------	------

Dimensions

Size	2-1/2 Inch/63mm
------	-----------------

Compliance and Certifications

RoHS	RoHS3 Compliant
REACH	REACH 253 Compliant
TSCA	TSCA Section 6(h) Compliant

ETIM	EC000464 Fixing clamp
Type of fastening	Clamping
Connection type construction part	Pipe/cable
Tube/cable diameter	63-63 mm
Hinging	N
Material	Other
Surface protection	Coated

by ABB

