



Representative Image

Catalog No. NPL21/2X12-G

Description: PVC CTD COND NIPPLE 2-1/2X12IN GRY

UPC No 704508398873

Home > Cable Protection Systems > Ocal > Electrical conduit nipple

PVC Coated Conduit Nipple, 2-1/2 Inch/63 Metric Pipe Size x 12 Inch/304.8 Millimeters Nipple Length, Nominal .002 Inch (2 mil) Blue Urethane on Interior, Minimum .040 Inch (40 mil) PVC Coating on Exterior, Blue Urethane Coating Over Threads, Hot-Dip Galvanized Rigid Steel, Gray

Descriptors

Category	Electrical conduit nipple
Special Features	A Minimum .040 Inch (40 Mil) PVC Coating on Exterior
Application	To Connect Two Fittings

Specifications

Material	Steel
Color	Gray
Finish	Hot-Dipped Galvanized

Classifications

Brand Name	Ocal
Standard	cULus E46453, CSA, RoHS

Dimensions

Length	12 in , 304.8 mm
Trade Size	2-1/2 in , 63 mm

Compliance and Certifications

RoHS	RoHS3 Compliant
REACH	REACH 247 Compliant
TSCA	TSCA Section 6(h) Compliant

ETIM	EC001469 Protective hose adapter
With outer thread	Y
Thread size outer thread metric	63
Material housing	Other
Surface protection	Hot dip galvanized


by ABB

ETIM	EC001469 Protective hose adapter
Model	Straight
Total length	304.8 mm