



Representative Image

Catalog No. NPL3X10-G

Description: PVC CTD COND NIPPLE 3X10IN STL GRY

UPC No 704508399979

Home > Cable Protection Systems > Ocal > Electrical conduit nipple

PVC Coated Conduit Nipple, 3 Inch/78 Metric Pipe Size x 10 Inch/254 Millimeters Nipple Length, Nominal .002 Inch (2 mil) Blue Urethane on Interior, Minimum .040 Inch (40 mil) PVC Coating on Exterior, Blue Urethane Coating Over Threads, Hot-Dip Galvanized Rigid Steel, Gray

Descriptors

Category	Electrical conduit nipple
Special Features	A Minimum .040 Inch (40 Mil) PVC Coating on Exterior
Application	To Connect Two Fittings

Specifications

Material	Steel
Color	Gray
Finish	Hot-Dipped Galvanized

Classifications

Brand Name	Ocal
Standard	cULus E46453, CSA, RoHS

Dimensions

Length	10 in , 254 mm
Trade Size	3 in , 78 mm

Compliance and Certifications

RoHS	RoHS3 Compliant
REACH	REACH 253 Compliant
TSCA	TSCA Section 6(h) Compliant

ETIM	EC001469 Protective hose adapter
With outer thread	Y
Thread size outer thread metric	78
Material housing	Other
Surface protection	Hot dip galvanized

by ABB

ETIM	EC001469 Protective hose adapter
Model	Straight
Total length	254 mm