



Representative Image

Catalog No. NPL3X39-G

Description: PVC CTD COND NIPPLE 3X39IN STL GRY

UPC No 704508008376

Home > Cable Protection Systems > Ocal > Electrical conduit nipple

PVC Coated Conduit Nipple, 3 Inch/78 Metric Pipe Size x 39 Inch/990.6 Millimeters Nipple Length, Nominal .002 Inch (2 mil) Blue Urethane on Interior, Minimum .040 Inch (40 mil) PVC Coating on Exterior, Blue Urethane Coating Over Threads, Hot-Dip Galvanized Rigid Steel, Gray

Descriptors

Category	Electrical conduit nipple
Special Features	A Minimum .040 Inch (40 Mil) PVC Coating on Exterior
Application	To Connect Two Fittings

Specifications

Material	Steel
Color	Gray
Finish	Hot-Dipped Galvanized

Classifications

Brand Name	Ocal
Standard	cULus E46453, CSA, RoHS

Dimensions

Length	39 in , 990.6 mm
Trade Size	3 in , 78 mm

ETIM	EC001469 Protective hose adapter
With outer thread	Y
Thread size outer thread metric	78
Material housing	Other
Surface protection	Hot dip galvanized
Model	Straight
Total length	990.6 mm