



Representative Image

Catalog No. NPL5X107/8-G

Description: PVC CTD COND NIPPLE 5X10-7/8IN GRY

UPC No 704508035105

Home > Cable Protection Systems > Ocal > Electrical conduit nipple

PVC Coated Conduit Nipple, 5 Inch/129 Metric Pipe Size x 10-7/8 Inch Nipple Length, Nominal .002 Inch (2 mil) Blue Urethane on Interior, Minimum .040 Inch (40 mil) PVC Coating on Exterior, Blue Urethane Coating Over Threads, Hot-Dip Galvanized Rigid Steel, Gray

Descriptors

Category	Electrical conduit nipple
Special Features	A Minimum .040 Inch (40 Mil) PVC Coating on Exterior
Application	To Connect Two Fittings

Specifications

Material	Steel
Color	Gray
Finish	Hot-Dipped Galvanized

Classifications

Brand Name	Ocal
Standard	cULus E46453, CSA, RoHS

Dimensions

Length	10-7/8 in
Trade Size	5 in , 129 mm

ETIM	EC001469 Protective hose adapter
With outer thread	Y
Thread size outer thread metric	129
Material housing	Other
Surface protection	Hot dip galvanized
Model	Straight
Total length	276.225 mm