



Representative Image

Catalog No. NPL5X81/4-G

Description: 5X8-1/4 IN GRAY PVC CTD NIPPLE STL

UPC No 704508036270

Home > Cable Protection Systems > Ocal > Electrical conduit nipple

PVC Coated Conduit Nipple, 5 Inch/129 Metric Pipe Size X 8-1/4 Inch Nipple Length, Nominal .002 Inch (2 Mil) Blue Urethane on Interior, Minimum .040 Inch (40 Mil) PVC Coating on Exterior, Blue Urethane Coating Over Threads, Hot-Dip Galvanized Rigid Steel, Gray

Descriptors

Category	Electrical conduit nipple
Special Features	A Minimum .040 Inch (40 Mil) PVC Coating on Exterior
Application	To Connect Two Fittings

Specifications

Material	Steel
Color	Gray
Finish	Hot-Dipped Galvanized

Classifications

Brand Name	Ocal
Standard	cULus E46453, CSA, RoHS

Dimensions

Length	8-1/4 in
Trade Size	5 in , 129 mm

ETIM	EC001469 Protective hose adapter
With outer thread	Y
Thread size outer thread metric	129
Material housing	Other
Surface protection	Hot dip galvanized
Model	Straight
Total length	209.55 mm