

Representative Image

Cat. No. NPL6X12SA-G

Description: PVC CTD COND NIPPLE 6X12IN AL GRY

UPC No 704508027759

Home > Cable Protection Systems > Ocal > Electrical conduit nipple

PVC Coated Conduit Nipple, 6 Inch/155 Metric Pipe Size x 12 Inch/304.8 Millimeters Nipple Length, Nominal .002 Inch (2 mil) Blue Urethane on Interior, Minimum .040 Inch (40 mil) PVC Coating on Exterior, Blue Urethane Coating Over Threads, Rigid Aluminum, Gray

Descriptors

Category	Electrical conduit nipple
Special Features	A Minimum .040 Inch (40 Mil) PVC Coating on Exterior
Application	To Connect Two Fittings

Specifications

Material	Aluminum
Color	Gray
Finish	PVC Coated

Classifications

Brand Name	Ocal
Standard	UL E221184

Dimensions

Length	12 in , 304.8 mm
Trade Size	6 in , 155 mm

ETIM	EC001469 Protective hose adapter
With outer thread	Y
Thread size outer thread metric	155
Material housing	Aluminium
Surface protection	Untreated
Model	Straight
Total length	304.8 mm

by ABB