



Representative Image

Catalog No. NPL6X8-G

Description: PVC CTD COND NIPPLE 6X8IN STL GRY

UPC No 704508400552

Home > Cable Protection Systems > Ocal > Electrical conduit nipple

PVC Coated Conduit Nipple, 6 Inch/155 Metric Pipe Size x 8 Inch/203.2 Millimeters Nipple Length, Nominal .002 Inch (2 mil) Blue Urethane on Interior, Minimum .040 Inch (40 mil) PVC Coating on Exterior, Blue Urethane Coating Over Threads, Hot-Dip Galvanized Rigid Steel, Gray

Descriptors

Category	Electrical conduit nipple
Special Features	A Minimum .040 Inch (40 Mil) PVC Coating on Exterior
Application	To Connect Two Fittings

Specifications

Material	Steel
Color	Gray
Finish	Hot-Dipped Galvanized

Classifications

Brand Name	Ocal
Standard	cULus E46453, CSA, RoHS

Dimensions

Length	8 in , 203.2 mm
Trade Size	6 in , 155 mm

Compliance and Certifications

RoHS	RoHS3 Compliant
REACH	REACH 253 Compliant
TSCA	TSCA Section 6(h) Compliant

ETIM	EC001469 Protective hose adapter
With outer thread	Y
Thread size outer thread metric	155
Material housing	Other
Surface protection	Hot dip galvanized

by ABB

ETIM	EC001469 Protective hose adapter
Model	Straight
Total length	203.2 mm