



Catalog No. PM815RFL

Description: LOAD CTR MCB 150A 8CKT N3R GRAY PON FTL

UPC No 783164641028

Home > Load Centers > Load Centers

PowerMark PRO main breaker plug-on neutral load centers arrive with a main circuit breaker installed for a convenient and swift install. Main circuit breakers allow for the user to stop the flow of electricity in the load center, shutting off all the power in the residence. The PM815RFL features spaces for 8 - 1" circuit breakers and 16 circuits, a 150-ampere bus rating, copper bus bars, factory installed feed-through lugs, and a NEMA 3R enclosure.

Descriptors

| | |
|-------------|--------------------|
| Category | Load Centers |
| GO Schedule | RI |
| Grouping | Single Phase - USA |

Specifications

| | |
|------------------------------|------------------------------|
| # Branch Circuit 250A | 8 |
| 1" Space | 8 |
| 1/2" Space | 0 |
| Amperage | 150 A |
| Circuit Breaker Style | Plug-On Neutral |
| Device type | Main Breaker |
| Door | Yes |
| Enclosure | Outdoor |
| Enclosure Type | Outdoor, Surface |
| Factory Installed Ground Kit | Bonding screw included |
| Feed | Top |
| Input/Output Voltage | 120/240V ac |
| Interrupt Rating | 22k |
| Interrupting Capacity Rating | 22 |
| Load Center Type | Plug-On Neutral Load Centers |
| NEMA Rating | NEMA 3R |
| No of Circuits | 16 |
| Phase | 1 Phase |
| Service & Voltage | 1 Phase, 3 Wire, 120/240V ac |
| Wires | 3 Wire |

Classifications

| | |
|----------------|----|
| UL/CUL Listing | UL |
|----------------|----|

Dimensions

| | |
|-------|----------|
| Depth | 3.805 in |
| Width | 14.11 in |