

Representative Image

Catalog No. SSB25B220

Description: PB2 STD-BRK BC 2500FR/2000CT

UPC No

Home > Circuit Breakers > Insulated Case Circuit Breakers > Power Break ™ II

Power Break II Insulated Case Circuit Breakers are highly compact, heavy-duty breakers that combine ease of use, asethetics and state-of-art performances in 200 through 4000-Amp frame sizes, rated for upto 200,000 Amps RMS symmetrical for 240Vac, in drawout and stationary versions.

Descriptors

Category	Power Break ™ II
Product Line	Power Break II
GO Schedule	245 A

Specifications

Frame Type	Power Break ™ II
Amperage	1000 A 1200 A 1500 A 1600 A 2000 A 750 A 800 A
System Voltage	120 Vac 120/240 Vac 240 Vac 277 Vac 480 Vac 600 Vac
Poles	3
Trip Indication Target	Yes
Continuous Current Rated	100 %
120 Vac Interrupting Rating	100 KAIC
120/240 Vac Interrupting Rating	100 KAIC
240 Vac Interrupting Rating	100 KAIC
277 Vac Interrupting Rating	100 KAIC
480 Vac Interrupting Rating	100 KAIC
600 Vac Interrupting Rating	85 KAIC
Suitable for Reverse Feed	Yes
Long Time	Adjustable
Short Time	Optional
Instantaneous	Adjustable
Ground Fault	Optional
Protective Relays	Optional
Communications	Optional
Current Metering	Standard

Specifications

Zone Selective Interlock	Optional
GSA Compliance	No

Classifications

UL File #	E11592
CSA File#	LR10263