



Representative Image

Catalog No. ST3/445-G

Description: PVC CTD LT COND CONN 45D 3/4IN DGRY

UPC No 704508407605

Home > Cable Protection Systems > Ocal > Liquid tight connectors

PVC Coated Liquitight Conduit Connector, 45 Degree, Pipe Size 3/4 Inch/21 Metric, Minimum .040 Inch (40 mil) PVC Coating on Exterior, Steel Fitting, Dark Gray

Descriptors

Category	Liquid tight connectors
Special Features	Pressure-Sealing Sleeves Protect the Connection
Application	To Positively Bond Conduit to Box or Enclosure

Specifications

Material	Steel
Finish	PVC Coated
Color	Dark Gray
Environmental Conditions	Hazardous Locations

Classifications

Brand Name	Ocal
------------	------

Dimensions

Size	3/4 Inch/21mm
------	---------------

Compliance and Certifications

RoHS	RoHS3 Compliant
REACH	REACH 247 Compliant
TSCA	TSCA Section 6(h) Compliant

ETIM	EC001180 Screw connection for protective metallic hose
Nominal diameter	21 mm
Nominal size in inch	3/4 inch
Model	45°-elbow
Revolving thread	N
Construction type	External thread

by ABB

ETIM	EC001180 Screw connection for protective metallic hose
Material housing	Steel
Surface protection	Other