

Representative Image

Catalog No. ST3/490-GN

Description: PVC CTD LT COND CONN 90D 3/4IN GRN

UPC No 704508028589

Home > Cable Protection Systems > Ocal > Liquid tight connectors

PVC Coated Liquitight Conduit Connector, 90 Degree, Pipe Size 3/4 Inch/21 Metric, Minimum .040 Inch (40 mil) PVC Coating on Exterior, Steel Fitting, Green

Descriptors

Category	Liquid tight connectors
Special Features	Pressure-Sealing Sleeves Protect the Connection
Application	To Positively Bond Conduit to Box or Enclosure

Specifications

Material	Steel
Finish	PVC Coated
Color	Green
Environmental Conditions	Hazardous Locations

Classifications

Brand Name	Ocal

Dimensions

Size	3/4 Inch/21mm

ETIM	EC001180 Screw connection for protective metallic hose
Nominal diameter	21 mm
Nominal size in inch	3/4 inch
Model	90°-elbow
Revolving thread	N
Construction type	External thread
Material housing	Steel
Surface protection	Other