



Representative Image

Catalog No. ST3/490SA-G

Description: PVCCTD LT COND CONN 90D 3/4IN AL GR

UPC No 704508407742

Home > Cable Protection Systems > Ocal > Liquid tight connectors

PVC Coated Liquitight Conduit Connector, 90 Degree, Pipe Size 3/4 Inch/21 Metric, Minimum .040 Inch (40 mil) PVC Coating on Exterior, Aluminum Fitting, Dark Gray

Descriptors

Category	Liquid tight connectors
Special Features	Pressure-Sealing Sleeves Protect the Connection
Application	To Positively Bond Conduit to Box or Enclosure

Specifications

Material	Aluminum
Finish	PVC Coated
Color	Dark Gray
Environmental Conditions	Hazardous Locations

Classifications

Brand Name	Ocal
------------	------

Dimensions

Size	3/4 Inch/21mm
------	---------------

Compliance and Certifications

RoHS	RoHS3 Compliant
------	-----------------

ETIM	EC001180 Screw connection for protective metallic hose
Nominal diameter	21 mm
Nominal size in inch	3/4 inch
Model	90°-elbow
Revolving thread	N
Construction type	External thread
Material housing	Other
Surface protection	Other

by ABB