



Representative Image

Catalog No. STE075-G

Description: PVC CTD STE FITTING HUB 3/4IN GRY

UPC No 704508430238

Home > Cable Protection Systems > Ocal > Electrical fittings

PVC Coated STE Series Fitting for Ordinary Locations, Hub Size 3/4 Inch/21 Metric, Strip Length 1.25 Inch, Gland Torque 600 Pounds Per Inch, Range Over Jacket Minimum 0.86 Inch - Maximum 1.21 Inch, Range Over Armor Minimum 0.78 Inch - Maximum 1.13 Inch, A1: Throat Diameter Minimum with End Stop 0.66 Inch, A2 Throat Diameter Minimum without End Stop 0.82 Inch, Dark Gray

Descriptors

Category	Electrical fittings
Special Features	Removable Armor-Stop for Greater Cable Ranges
Application	Provide Means for Passing Armored, Metal Clad, Jacketed or Unjacketed and Unarmored Cables Through a Bulkhead or Enclosure in Hazardous Areas

Specifications

Material	Aluminum
Enclosure	NEMA 6P
Color	Gray

Classifications

Brand Name	Ocal
Standard	UL E38947

Dimensions

Size	3/4 Inch/21mm
------	---------------

Compliance and Certifications

RoHS	RoHS3 Compliant
REACH	REACH 253 Compliant
TSCA	TSCA Section 6(h) Compliant

ETIM	EC001180 Screw connection for protective metallic hose
Nominal diameter	21 mm
Nominal size in inch	3/4 inch
Model	Straight
Revolving thread	N

by ABB

ETIM	EC001180 Screw connection for protective metallic hose
Construction type	External thread
Material housing	Other
Surface protection	Other