



Representative Image

Catalog No. STE100-G

Description: PVC CTD STE FITTING HUB 1IN GRY

UPC No 704508430245

Home > Cable Protection Systems > Ocal > Electrical fittings

PVC Coated STE Series Fittings for Ordinary Locations, Hub Size 1 Inch/27 Metric, Strip Length 1.25 Inch, Gland Torque 700 Pounds Per Inch, Range Over Jacket Minimum .95 Inch - Maximum 1.38 Inch, Range Over Armor Minimum 0.87 Inch - Maximum 1.30 Inch, A1:throat Diameter Minimum with End Stop .79 Inch, A2: Throat Diameter Minimum without End Stop 1.04 Inch, Gray

Descriptors

Category	Electrical fittings
Special Features	Removable Armor-Stop for Greater Cable Ranges
Application	Provide Means for Passing Armored, Metal Clad, Jacketed or Unjacketed and Unarmored Cables Through a Bulkhead or Enclosure in Hazardous Areas

Specifications

Material	Aluminum
Enclosure	NEMA 6P
Color	Gray

Classifications

Brand Name	Ocal
Standard	UL E38947

Dimensions

Size	1 Inch/27mm
------	-------------

Compliance and Certifications

RoHS	RoHS3 Compliant
TSCA	TSCA Section 6(h) Compliant

ETIM	EC001180 Screw connection for protective metallic hose
Nominal diameter	27 mm
Nominal size in inch	1 inch
Model	Straight
Revolving thread	N
Construction type	External thread

by ABB

ETIM	EC001180 Screw connection for protective metallic hose
Material housing	Other
Surface protection	Other