



Catalog No. STEX075-G

Description: PVC CTD STEX FITTING HUB 3/4IN GRY

UPC No 704508018580

Home > Cable Protection Systems > Ocal > Electrical fittings

PVC Coated STEX Series Fittings for Hazardous Locations, Hub Size 3/4 Inch/21 Metric, Strip Length 1.25 Inch, Gland Torque 600 Pounds Per Inch, Range Over Jacket Minimum .60 Inch - Maximum .99 Inch, Range Over Armor Minimum .52 Inch - Maximum .90 Inch, A1: Throat Diameter Minimum with End Stop .50 Inch, A2: Throat Diameter Minimum without End Stop .68 Inch, Gray

Descriptors

Category	Electrical fittings
Special Features	Removable Armor-Stop for Greater Cable Ranges
Application	Provide Means for Passing Armored, Metal Clad, Jacketed or Unjacketed and Unarmored Cables Through a Bulkhead or Enclosure in Hazardous Areas

Specifications

Material	Aluminum
Enclosure	NEMA 4, 4X, 6P
Color	Gray

Classifications

Brand Name	Ocal
------------	------

Dimensions

Size	3/4 Inch/21mm
------	---------------

Compliance and Certifications

RoHS	RoHS3 Compliant
REACH	REACH 240 Compliant
TSCA	TSCA Section 6(h) Compliant

ETIM	EC001180 Screw connection for protective metallic hose
Nominal diameter	21 mm
Nominal size in inch	3/4 inch
Model	Straight
Revolving thread	N
Construction type	External thread

by ABB

ETIM	EC001180 Screw connection for protective metallic hose
Material housing	Other
Surface protection	Other