



Catalog No. STEX100-G

Description: PVC CTD STEX FITTING HUB 1IN GRY

UPC No 704508033521

Home > Cable Protection Systems > Ocal > Electrical fittings

PVC Coated STEX Series Fittings for Hazardous Locations, Hub Size 1 Inch/27 Metric, Strip Length 1.25 Inch, Gland Torque 700 Pounds Per Inch, Range Over Jacket Minimum .86 Inch - Maximum 1.21 Inch, Range Over Armor Minimum .87 Inch - Maximum 1.13 Inch, A1: Throat Diameter Minimum with End Stop .65 Inch, A2: Throat Diameter Minimum without End Stop .83 Inch, Gray

Descriptors

Category	Electrical fittings
Special Features	Removable Armor-Stop for Greater Cable Ranges
Application	Provide Means for Passing Armored, Metal Clad, Jacketed or Unjacketed and Unarmored Cables Through a Bulkhead or Enclosure in Hazardous Areas

Specifications

Material	Aluminum
Enclosure	NEMA 4, 4X, 6P
Color	Gray

Classifications

Brand Name	Ocal
------------	------

Dimensions

Size	1 Inch/27mm
------	-------------

ETIM	EC001180 Screw connection for protective metallic hose
Nominal diameter	27 mm
Nominal size in inch	1 inch
Model	Straight
Revolving thread	N
Construction type	External thread
Material housing	Other
Surface protection	Other

by ABB