



Representative Image

Catalog No. STG1-G

Description: PVC CTD ZINC GROUND HUB 1/2IN DGRAY

UPC No 704508408732

Home > Cable Protection Systems > Ocal > Electrical fittings

PVC Coated Zinc Grounded Hub with Thermoplastic Insulated Throat, Pipe Size 1/2 Inch/16 Metric, Overall Diameter 1.44 Inch/36.58 Millimeters, Maximum Panel Thickness 0.19 Inch/4.83 Millimeters, Throat Diameter 0.59 Inch/14.99 Millimeters, Nitrile Rubber (Buna-N) Sealing Ring, Dark Gray

Descriptors

Category	Electrical fittings
Special Features	Hexagonal/Splined Body and Locknut Enables Fast and Easy Installation
Application	To Positively Bond Conduit to Box or Enclosure

Specifications

Material	PVC Coated Zinc
Color	Dark Gray
Temperature Rating	105 C

Classifications

Brand Name	Ocal
------------	------

Dimensions

Size	1/2 Inch/16mm
------	---------------

Compliance and Certifications

RoHS	RoHS3 Compliant
TSCA	TSCA Section 6(h) Compliant

ETIM	EC001180 Screw connection for protective metallic hose
Nominal diameter	16 mm
Nominal size in inch	1/2 inch
Model	Straight
Revolving thread	N
Construction type	External thread
Material housing	Other
Surface protection	Other

by ABB

