



Catalog No. STG6-GN

Description: PVC CTD ZINC GROUND HUB 2IN GREEN

UPC No 704508028602

Home > Cable Protection Systems > Ocal > Electrical fittings

PVC Coated Zinc Grounded Hub with Thermoplastic Insulated Throat, Pipe Size 2 Inch/53 Metric, Overall Diameter 3.25 Inch/82.55 Millimeters, Maximum Panel Thickness 0.25 Inch/6.35 Millimeters, Throat Diameter 1.97 Inch/50.04 Millimeters, Nitrile Rubber (Buna-N) Sealing Ring, Green

Descriptors

Category	Electrical fittings
Special Features	Hexagonal/Splined Body and Locknut Enables Fast and Easy Installation
Application	To Positively Bond Conduit to Box or Enclosure

Specifications

Material	PVC Coated Zinc
Color	Green
Temperature Rating	105 C

Classifications

Brand Name	Ocal
------------	------

Dimensions

Size	2 Inch/53mm
------	-------------

Compliance and Certifications

RoHS	RoHS3 Compliant
TSCA	TSCA Section 6(h) Compliant

ETIM	EC001180 Screw connection for protective metallic hose
Nominal diameter	53 mm
Nominal size in inch	2 inch
Model	Straight
Revolving thread	N
Construction type	External thread
Material housing	Other
Surface protection	Other

by ABB

