



Catalog No. STX050464-G

Description: PVC CTD STX FTG 1/2IN ALUM GRAY

UPC No 704508027940

Home > Cable Protection Systems > Ocal > Electrical fittings

PVC Coated Aluminum STX Series Fittings for Hazardous Location, Hub Size 1/2 Inch/16 Metric, Strip Length 1.25 Inch, Gland Torque 300 Pounds Per Inch, Range Over Jacket Minimum 0.60 Inch - Maximum 0.76 Inch, Range Over Armor Minimum 0.49 Inch - Maximum 0.68 Inch, A2 Throat Diameter Minimum without End Stop 0.49 Inch, Gray

Descriptors

Category	Electrical fittings
Special Features	Flame Path is Optimally Designed to Allow for Easy Insertion Into Hub
Application	Provide Means for Passing Armored, Metal Clad, Jacketed or Unjacketed and Unarmored Cables Through a Bulkhead or Enclosure in Hazardous Areas

Specifications

Material	Aluminum
Color	Gray

Classifications

Brand Name	Ocal
------------	------

Dimensions

Size	1/2 Inch/16mm
------	---------------

Compliance and Certifications

RoHS	RoHS3 Compliant
REACH	REACH 240 Compliant
TSCA	TSCA Section 6(h) Compliant

ETIM	EC001180 Screw connection for protective metallic hose
Nominal diameter	16 mm
Nominal size in inch	1/2 inch
Model	Straight
Revolving thread	N
Construction type	External thread
Material housing	Other

by ABB

ETIM	EC001180 Screw connection for protective metallic hose
Surface protection	Other